

# Eaton 7504GY-BOX

Catalog Number: 7504GY-BOX

Eaton standard grade decorator switch, Box, #14-12 AWG, 15A, Flush, 120/277V, Back/push, Decorator, Maintained, Gray, Motor Control, Fan, LED, Incand, ELV,MLV,CFL, Florscnt, Halogen, Four-way, Thermoplastic 644696



## General specifications

Product Name	Catalog Number
Eaton standard grade decorator switch	7504GY-BOX
UPC	Product Length/Depth
032664644696	1.44 in
Product Height	Product Width
4.19 in	0.97 in
Product Weight	Compliances
0.001 lb	RoHS Compliant
	NAFTA
Certifications	
cULus Listed	

## Product specifications

### Special features

Box

### Switch type

Four-way

### Phase

Single-phase

### Load type

CFL

MLV

LED

HAL

ELV

INC

Fan

Motor Control

FLR

### Closure type

Maintained

### Color

Gray

### Wiring method

Back and push

### Material

Thermoplastic

### Mounting method

Flush

### Allowable wire size

#14-12 AWG

### Amperage Rating

15A

### Number Of Poles

Four-way

### Type

Switch decorator

### Voltage rating

120/277 V

## Resources

### Catalogs

[Residential Buyers Guide B-04](#)

### Specifications and datasheets

[Eaton Specification Sheet - 7504GY-BOX](#)

Actuator  
Decorator



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)