




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1105 West Sanger
88240-0000, NM Hobbs
Phone: 575-397-2122
Fax: 575-397-2178



80PVC1 SCH 80 1" 10' PVC Conduit

Heritage Plastics

Catalog Number	80PVC1
Manufacturer	Heritage Plastics
Description	PVC Conduit, Underground or Aboveground Application, Gray Color, 0.910 In Conduit Inner Diameter, 1.315 In Conduit Outer Diameter, 10 FT Length, Made In Usa, +90 °C Maximum Operating Temperature, 3600 FT/PK Package Quantity, Belled End;Corrosion Resistant;Rust Resistant;Sunlight Resistant;Rated For 90° Cable;Rigid Nonmetallic PVC Schedule 80 Special Features, Intertex Etl Listed Us;UI 651 and Nema TC2 Standards Met, 1 In Trade Size, 0.179 In Wall Thickness, 0.412 LB Weight
Weight per unit	0.4120 (lbs/each)
Product Category	PVC SCH 80 Conduit

Descriptions

Description	SCH 80 1" 10' PVC CONDUIT
extra long description	AL-TUBE 9304 PVC SCH80 1 x 10 UL BE

Manufacturer Information

GTIN	00091111093043
Manufacturers Part Number	A53BA12
UPC	091111093043

Taxonomies, Classifications, and Categories

Category Description	PVC Schedule 80 Conduit
----------------------	-------------------------

Availability

minimum qty	10
-------------	----

Packaging

Carton	10
Package	3600
Weight Per foot	0.412