



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



837211 Vinyl Insul Spade Termnl 12-10AWG, #8 Stud, 25/Box

Ideal

Catalog Number	837211
Manufacturer	Ideal
Description	Spade Terminal, #12 Awg Conductor Size, #10 Awg Conductor Size, Insulated, Vinyl Insulation Material, Brass Conductor Material, 1.004 In Overall Length, 0.248 In Insulation Length, 0.01 LB
Weight per unit	0.2000 (lbs/each)
Product Category	Small Terminals & Connectors

Features

Cable Size	12 - 10
insulation	Vinyl Insulated
Material	TIN PLATED BRASS
Stud Size	8

Descriptions

Description	VINYL INSUL SPADE TERMNL 12-10AWG, #8 STUD, 25/BOX
extra long description	IDEAL 83-7211 TERMINAL, VINYL SPADE
Features	Butted seam-construction prevents splitting under maximum pressureInternal barrel serrations grip wires tightly to resist pull-out and reduce electrical resistanceTin-plated brass construction for corrosion resistanceShouldered barrel insulation quickly positions terminal for proper crimpingExpanded insulation entry accommodates a wide variety of insulation diameters and provides additional insulation supportThe complete line of IDEAL crimp terminals, disconnects, and splices offer the right product for an

Manufacturer Information

Brand	Ideal
GTIN	00783250490196
UPC	783250490196

Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCK ACESSORIES
Type	Vinyl Spade

Availability

minimum qty	25
-------------	----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	25
Weight Per each	0.2

Uses, Certifications, and Standards

standard	UL Listed, RoHS
----------	-----------------