

## **RG-59 F Twist-on Connector**

Traditional style twist-on connector for indoor video applications. Cable specific sizing for a termination to RG-59 coax cables. Twist-on style are removable and reusable.



- Single piece design
- · No termination tool required
- · Knurled body for a better grip while twisting
- · Designed for indoor applications
- 1GHZ,  $75\Omega$  rated for use in basic video applications
- 7/16" hex nut
- Fits cables with .230" .250" jacket diameter
- Fits cables with .142" .148" dielectric diameter
- Requires industry standard ¼" x ¼" cable preparation
- Recommended IDEAL cable prep tool: 45-605



Part No.	Qty
84-014	4/Card
85-035	10/Card

Also available:



92-610 59F Compression



85-036 59F Crimp