


TLC™ RG-6 F Tool-Less Compression Connector

Get many of the benefits of a 360° compression connector without the need to use a compression tool. Cable specific connector for RG-6. Just prep the cable and slide it on for a permanent connection.

- No compression tool required
- Designed for indoor applications
- Connector locks in place on cable jacket for a permanent connection
- Faster and easier to use than traditional twist on connectors
- Patented 360° grip on cable prevents cable and dielectric deformation that result in signal loss
- 3GHZ, 75Ω rated for use in all video based applications such as cable and satellite television
- >50lbs cable retention
- Fits cables with .254" .278" jacket diameter
- Fits cables with .175" .183" dielectric diameter
- Only requires industry standard 1/4" x 1/4" cable preparation
- Recommended IDEAL cable prep tool: 45-605





45-605

Part NO.	Qiy			
85-069	4/Card	Also available:		
85-068	10/Card			
85-168	50/Card			
			O	

85-178 RG-6 Quad TLC™

92-650 RTQ™ XR™

© IDEAL INDUSTRIES, INC.