

## OmniConn™ RG-6 F Compression Connector

Cable specific RG-6 coax F compression connector designed for indoor and outdoor applications. Blue adapter sleeve provides a weatherproof back seal once compressed.

- Nickel plated brass and plastic construction for indoor/outdoor applications
- · O-ring and adapter sleeve prevent moisture migration
- 3GHZ, 75Ω rated for use in all video based applications such as cable and satellite television
- >40lbs cable retention
- Fits cables with .260" .280" jacket diameter
- Fits cables with .175" .183" dielectric diameter
- Requires industry standard ¼" x ¼" cable preparation
- Recommended IDEAL cable prep tool: 45-605
- · Requires industry standard 21mm compression stroke
- Recommended compression tools: 30-793, 33-632
- Compatible with non-IDEAL tools
- Not compatible with 35-046 F/BNC Insertion Tool

Part No.	Qty
89-019	10/Card
89-044	50/Jar
89-1544	1,000/Bulk Box

## Also available:







89-045 RG-6 Quad OmniConn™

45-605

30-793



