



## Terminal Strip, 12-Circuit (Box of 10)



### Features

- Torque Rating of 16 in-lbs
- Rugged base eliminates breakage
- Center spacing of 0.562 inch (14.3mm)
- Accepts up to #10 AWG wire
- Corrosion resistant surface plates with #8 philslot screws
- Rated up to 600V, 30A
- Accessory jumpers available

### Models

Description	Catalog #
Terminal Strip, 12-Circuit (Box of 10)	89-212