


## **InSITE™ RG-59 BNC Compression Connector**

BNC compression connector for RG-59 coax cables. InSITE™ technology to verify cable is fully seated in the connector before compression. Simplifies security camera installations.

- Nickel plated brass external construction with gold plated fixed center pin contact
- InSITE™ window allows verification of proper cable insertion before compressing the connector
- 3GHZ,  $75\Omega$  rated for use in all video based applications such as security cameras and video distribution
- Fits cables with .230" .250" jacket diameter
- Fits cables with .142" .148" dielectric diameter
- Fits cables with 23-18 AWG solid center conductor
- Requires industry standard ¼" x ¼" cable preparation
- Recommended IDEAL cable prep tool: 45-605
- Recommended compression tools: 30-793, 33-632
- Compatible with non-IDEAL tools

Part No.	Qty
92-704	4/Card
89-047	15/Card
89-5047	35/Jar

Also available:









92-693

30-793

© IDEAL INDUSTRIES, INC.