



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A20SA2208LP 20X22X8 N12 CH Discnct Encl

*Hoffman Enclosures, Inc.*

Catalog Number	A20SA2208LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Disconnect Enclosure Without Handle Type 12, 20X21.38X8, Gray, Steel
Weight per unit	38.1 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

### Features

ip rating	IP65
Material	MILD STEEL

### Material, Color, and Finish

Finish	Powder Coated
--------	---------------

### Dimensions and Weight

Depth	8
Height	20
Size	20.00x21.38x8.00 in
Width	21.38

### Descriptions

Description	20X22X8 N12 CH DISCNCT ENCL
extra long description	NVENT HOF A20SA2208LP Disconnect En
Features	These general purpose disconnect enclosures accept major brand disconnect switches and circuit breakers, available with or without the nVent HOFFMAN supplied defeater door handle and handle hardware.
Long Description	Disconnect Enclosure without Handle Type 12, 20x21.38x8, Gray, Steel
Product Type	Disconnect Encl. 20.00X21.38X8

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510328009
Manufacturers Part Number	A20SA2208LP
UPC	783510328009

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Disconnect Enclosures

### Packaging

Carton	1
Weight Per each	38.12



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....	Controls and Drives; Power Distribution; Arc Flash Safety .....
nema rating .....	12 Indoor, dust-resistant .....