



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A24R2412 24X24X12 N3R SC

Hoffman Enclosures, Inc.

Catalog Number	A24R2412
Manufacturer	Hoffman Enclosures, Inc.
Description	Screw-Cover Drip-Shield Type 3R With Knockouts, 24X24X12, Gray, Steel
Weight per unit	55.1 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

Features

ip rating	IP32
Knockouts	Yes
Material	Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

Dimensions and Weight

Depth	12
Size	24.00x24.00x12.00 in
Width	24

Descriptions

Description	24X24X12 N3R SC
extra long description	NVENT HOF A24R2412 Type 3R Enclosur
Features	Drip-Shield Screw-Cover, Type 3R is used as a wiring or junction box to protect controls in outdoor applications that require protection from rain, sleet, snow or dripping water.
Long Description	Screw-Cover Drip-Shield Type 3R With Knockouts, 24x24x12, Gray, Steel
Product Type	Type 3R Enclosure, Screw Cover

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510386207
Manufacturers Part Number	A24R2412
UPC	783510386207

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Pull and Junction Boxes



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	55.0999

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	3R Weather-resistant, except dust