



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A36H2410SS6LP 36X24X10 N4X CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A36H2410SS6LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 36X24X10, Brushed, SS316
Weight per unit	75.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel 316L

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	10
Height	36
Size	36.00x24.00x10.00 in
Width	24

Descriptions

Description	36X24X10 N4X CH CLMP CVR
extra long description	NVENT HOF A36H2410SS6LP Stainless E
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 36x24x10, Brushed, SS316
Product Type	Stainless Encl. 36.00X24.00X10

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510837303
Manufacturers Part Number	A36H2410SS6LP
UPC	783510837303

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	75

Uses, Certifications, and Standards

Application	Corrosive Environments, Controls and Drives
nema rating	4X Watertight, corrosion-resistant