



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A36H3012GQRLP 36.25X30.25X12 N4X FG QR HC

Hoffman Enclosures, Inc.

Catalog Number	A36H3012GQRLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Hinge Cover Enclosure Quick-Release Type 4X, 36.25X30.25X12.00, Gray, Fiberglass
Weight per unit	52.9 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
Material	Fiberglass

Material, Color, and Finish

Color	Gray
Finish	Smooth Matte

Dimensions and Weight

Depth	12
Height	36.25
Size	36.25x30.25x12.00 in
Width	30.25

Descriptions

Description	36.25X30.25X12 N4X FG QR HC
extra long description	NVENT HOF A36H3012GQRLP Enclosure 3
Features	A full range of modification options are available for wall-mount fiberglass enclosures, including variable depths to accommodate larger controls. These enclosures feature padlockable polyester latches, or HOFFMAN's exclusive PowerGlide Handle with 3-point latching, for ease of access with increased security.
Long Description	Hinge Cover Enclosure Quick-Release Type 4X, 36.25x30.25x12.00, Gray, Fiberglass
Product Type	Enclosure 36.25X30.25X12.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510226602
Manufacturers Part Number	A36H3012GQRLP
UPC	783510226602

Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	52.9

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant