



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A484814HCT 48X48X14 N3R HNGD Transformer CBNT

*Hoffman Enclosures, Inc.*

Catalog Number	A484814HCT
Manufacturer	Hoffman Enclosures, Inc.
Description	Current Transformer Hinged Cover, 48.00X48.00X14.00, Gray, Steel
Weight per unit	213.0 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

### Features

ip rating	IP32
Material	MILD STEEL

### Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

### Dimensions and Weight

Depth	14
Size	48.00x48.00x14.00 in
Width	48

### Descriptions

Description	48X48X14 N3R HNGD TRANSFORMER CBNT
extra long description	NVENT HOF A484814HCT CT Cabinet Hin
Features	CT Cabinet Hinged-Cover, Type 3R provide outdoor protection and security for instrument current transformers, which are frequently required for transformer-rated watt-hour metering. Cabinets can also be used as junction or service boxes and house meter, transformer, relay or terminal assemblies.
Long Description	Current Transformer Hinged Cover, 48.00x48.00x14.00, Gray, Steel
Product Type	CT Cabinet Hinged Double Door

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510153069
Manufacturers Part Number	A484814HCT
UPC	783510153069

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Utility / Canadian Cabinets and Splitters



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	213

## Uses, Certifications, and Standards

Application	Power Distribution; Controls and Drives
nema rating	3R Weather-resistant, except dust