



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A500391A 16/2 Oas 1000' Reel

*Southwire Company*

|                  |   |
|------------------|---|
| Catalog Number   | A500391A  |
| Manufacturer     | Southwire Company   |
| Description      | Multi-Conductor Cable, Stranded, 16 Strands, 300 V, 1000 FT Overall Length, 0.187 In Outside Diameter, 19/0.0117 MM Core Strands, Copper Conductor Material, PVC Insulation Material, PVC Jacket Material, Black;Red, +60 °C Operating Temperature, 0.028 LB/Ea |
| Weight per unit  | 0.0280 (lbs/ft)   |
| Product Category | Non-Plenum Shielded Cable   |

### Features

|                      |          |
|----------------------|----------|
| amperage rating      | CL3      |
| Conductor Size       | 16       |
| core                 | SHIELDED |
| Number of Conductors | 2        |
| Resistance           | 4.35     |
| strands              | 19       |

### Material, Color, and Finish

|        |      |
|--------|------|
| Finish | BULK |
|--------|------|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Construction           | CABLE                               |
| Description            | 16/2 OAS 1000' REEL                 |
| extra long description | SWC A50039-1A SY 16/2 STR BC OAS CM |
| Special Features       | CL3R                                |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Cables & Cords |
| GTIN                      | 00032886882432 |
| Manufacturers Part Number | A50039-1A      |
| UPC                       | 032886882432   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Portable Cords, Voice, Data, Video Wire & Cable |
| Type                 | CMR   |

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1000  |
| Weight Per foot | 0.028 |

### Uses, Certifications, and Standards

|                    |        |
|--------------------|--------|
| standard           | UL 444 |
| Temperature Rating | 60     |