

# Eaton AC-20C20

Catalog Number: AC-20C20

Eaton B-Line series consolelet enclosures, 20" height, 13.12" length, 20" width, NEMA 12, Hinged cover, AC consolelet, Surface mounted, Medium single door, External mounting feet, Carbon steel, Oil-resistant gasket

## General specifications



Product Name	Catalog Number
Eaton B-Line series consolelet enclosures	AC-20C20
UPC	Product Length/Depth
782051410204	13.12 in
Product Height	Product Width
20 in	20 in
Product Weight	Certifications
31 lb	UL 508A
	CSA C22.2.
	NEMA

Material/finish	Model
<a href="#">Material</a> Carbon steel	<a href="#">Style</a> Medium single door
<a href="#">Wall thickness</a> 14 gauge	<a href="#">Model</a> AC console
<a href="#">Finish color</a> Painted	<a href="#">Cover type</a> Hinged
<a href="#">Color</a> ANSI 61 gray	<a href="#">Mounting method</a> Surface
	<a href="#">Mounting hole details</a> External mounting feet
	<a href="#">Closure type</a> Hinged
	<a href="#">Special features</a> Continuous hinge, plated screws
Standards	Resources
<a href="#">NEMA Rating</a> 12	<a href="#">Catalogs</a> <a href="#">Pushbutton-enclosure-operator.pdf</a>
<a href="#">Country of origin</a> US	<a href="#">Specifications and datasheets</a> <a href="#">Eaton Specification Sheet - AC-20C20</a>