



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AL2DCCW Adjustable Plated Steel Latch Kit

Hoffman Enclosures, Inc.

Catalog Number	AL2DCCW
Manufacturer	Hoffman Enclosures, Inc.
Description	Latch Kit 1-Door Type 12 Enclosure Keylock CCW, 3-PT (HT=60TO72), Chrome, Steel
Weight per unit	3.7 (lbs/each)
Product Category	Enclosure General Accessories

Features

accessory type	Locks, Lockouts, Latches, Handles and Clamps
Handle Type	Keylock
Material	MILD STEEL

Material, Color, and Finish

Color	Unpainted
Finish	Brushed Chrome

Dimensions and Weight

Size	3 Point (A=60to72) in
------	-----------------------

Descriptions

Description	ADJUSTABLE PLATED STEEL LATCH KIT
extra long description	NVENT HOF AL2DCCW NEMA12 3PT LATCH
Features	Designed for field installation on most standard one-door Type 12 enclosures. These latch kits will not fit HOFFMAN disconnect, Concept or ProLine enclosures. The latch rods can be adjusted to maintain the proper gasket compression by relocating the pins in the rod guides. When the pin is removed, the latch rod can also be removed. All openings through the door are gasketed to assure a complete seal. Ends of latch rods have rollers for easier door closing.
Long Description	Latch Kit 1-Door Type 12 Enclosure Keylock CCW, 3-Pt (Ht=60to72), Chrome, Steel
Product Type	NEMA12 3PT Latch CCW Keyl PLT

Manufacturer Information

Brand	Hoffman Enclosures, Inc.
GTIN	00783510228002
Manufacturers Part Number	AL2DCCW
UPC	783510228002

Taxonomies, Classifications, and Categories

Type	Industrial Door Mounting and Locks
------	------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	3.7

Uses, Certifications, and Standards

Application	Controls and Drives; Power Distribution
nema rating	12 Indoor, dust-resistant