

Eaton AN16AN0AC

Catalog Number: AN16AN0AC

Eaton Freedom NEMA motor control starter, 1/3 hp at 115V, 1 hp at 230V, 1-1/2 hp at 208,240V, 2 hp at 480,600V maximum horsepower, 120V/60 Hz or 110V/50 Hz coil voltage, 9A, Size 00



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN16AN0AC
	UPC
	782113971414
Product Length/Depth	Product Height
4.61 in	3.31 in
Product Width	Product Weight
4.38 in	2.6 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed
	Catalog Notes
	Heater Packs must be purchased separately

defaultTaxonomyAttributeLabel

Special features

Starter w/C306 bi-metal OLR

HP rating - max

1/3 hp at 115V, 1 hp at 230V, 1-1/2 hp at 208,240V, 2 hp at 480,600V

Phase

Single-phase, three-phase

Amperage Rating

9A

Size

0

Mounting

Horizontal

Coil voltage

110-120 Vac, 50/60 Hz

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[AN16AN0_C AutoCAD 2D Footprint](#)

[AN16AN0_C 2D PDF](#)

[AN16AN0_C 3D Model Xchange](#)

[AN16AN0_C 3D Inventor](#)

[AN16AN0_C AutoCAD 2D Footprint \(mm\)](#)

[AN16AN0_C 2D Drawing Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - AN16AN0AC](#)

[Quick Selector - NEMA Contactors](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)