

# Eaton AN16GN0AB

Catalog Number: AN16GN0AB

Eaton Freedom NEMA motor control starter, Non-Reversing Reset Overload Relay Starter, 120V/60 Hz or 110V/50 Hz coil voltage, 45A, Three-pole, Size 2



## General specifications

<a href="#">Product Name</a>	<a href="#">Catalog Number</a>
Eaton Freedom NEMA motor control starter	AN16GN0AB
	<a href="#">UPC</a>
	782113971841

<a href="#">Product Length/Depth</a>	<a href="#">Product Height</a>
4.94 in	3.31 in

<a href="#">Product Width</a>	<a href="#">Product Weight</a>
4.38 in	3.3 lb

<a href="#">Warranty</a>	<a href="#">Certifications</a>
--------------------------	--------------------------------

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

CSA Certified

[Catalog Notes](#)

Heater Packs must be purchased separately

## defaultTaxonomyAttributeLabel

### Special features

Starter w/C306 bi-metal OLR

### HP rating - max

3 hp at 115V, 7-1/2 hp at 230V, 10 hp at 208V, 15 hp at 240V,  
25 hp at 480,600V

### Phase

Single-phase, three-phase

### Amperage Rating

45A

### Size

2

### Mounting

Horizontal

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[AN16GN0\\_B AutoCAD 2D Footprint](#)

[AN16GN0\\_B 2D PDF](#)

[AN16GN0\\_B AutoCAD 2D Footprint \(mm\)](#)

[AN16GN0\\_B 3D Model Xchange](#)

[AN16GN0\\_B 3D Inventor](#)

[AN16GN0\\_B 2D Drawing Xchange](#)

### Specifications and datasheets

[Eaton Specification Sheet - AN16GN0AB](#)

[Quick Selector - NEMA Contactors](#)

### Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)