

Eaton AN19GN0A5G045

Catalog Number: AN19GN0A5G045

Eaton Freedom NEMA Starter, Full voltage non-reversing, C440 electronic overload relay, NEMA Size 2 open enclosure - 45 A, Horizontal mounting, 120/60 or 110/50 coil voltage, C440 ground fault feature set - 9–45 A



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN19GN0A5G045
	UPC
	786685415437
Product Length/Depth	Product Height
4.98 in	7.1 in
Product Width	Product Weight
2.6 in	4 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
UL	
CSA	
CE	
NEMA	

defaultTaxonomyAttributeLabel

NEMA frame size

NEMA Size 2

Relay

C440 electronic

Type

Starter

Special features

With C440 EOLR ground fault feature set, SEL reset, SEL class (10, 20)

Configuration

Non-reversing

Amperage Rating

45 A

Size

2

Mounting

Horizontal

Overload relay

C440 electronic

Coil voltage

120/60 or 110/50

Resources

Catalogs

Eaton's Volume 5—Motor Control and Protection

Drawings

AN19GN0_5 AutoCAD 2D Footprint

AN19GN0_5 3D Model Xchange

AN19GN0_5 3D Inventor

AN19GN0_5 2D PDF

AN19GN0_5 2D Drawing Xchange

AN19GN0_5 AutoCAD 2D Footprint (mm)

Specifications and datasheets

Eaton Specification Sheet - AN19GN0A5G045



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia