Product specifications

Eaton AR1041

Catalog Number: AR1041

Eaton Crouse-Hinds series Arktite AR receptacle, 100A, Four-wire, four-pole, 50-400 Hz, Style 1, Copper-free aluminum, Spring door, 600 Vac/250 Vdc

General specifications

Product Name Catalog Number

Eaton Crouse-Hinds series Arktite AR AR1041

receptacle

UPC

782274064802

Product Length/Depth Product Height

5.25 in 4.25 in

Product Width Product Weight

4.25 in 3.7 lb



Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Amperage Rating

100A

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Grounding type

Style 1

Configuration

Four-wire, four-pole

Receptacle style

Spring door

Material

Copper-free aluminum

Resources

3D CAD drawing package

Eaton Crouse-Hinds AR1041 3D drawing

Catalogs

Arktite 100A Metallic Plugs, Receptacles and Connectors catalog page

Certification reports

Arktite Metallic Plugs, Receptacles and Connectors UL certification (AR)

Installation instructions

IF 352 - Model M72 Arktite Plugs and Receptacles

IF 1229 - Arktite Plugs and Receptacles, Model M4, 30, 60, 100A

Specifications and datasheets

Eaton Specification Sheet - AR1041



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2023 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia