

Eaton B54-120 SS4

Catalog Number: B54-120 SS4

Eaton B-Line series strut channel, .81" channel height, 120" channel length, 1.62" channel width, Steel, 14 Gauge, B54 channel type, Stainless steel type 304



General specifications

Product Name	Catalog Number
Eaton B-Line series strut channel	B54-120 SS4
UPC	Product Length/Depth
781011255138	120 in
Product Height	Product Width
0.81 in	1.62 in
Product Weight	Certifications
10.16 lb	Not Applicable

Model

Channel type

B54

Material/finish

Finish

Stainless steel type 304

Material

Steel

Material gauge

14 Gauge

Resources

Brochures

[Strut Channel Identification Overview](#)

Catalogs

[Strut Systems Full Catalog](#)

[Aluminum and Stainless Steel Materials Catalog Section](#)

[KwikSplice Cable Tray USA Stocking List Flyer](#)

[Channel and Combinations Catalog Section](#)

Installation instructions

[KwikSplice Cable Tray System Tab and Lock Trapeze Support](#)

[KwikSplice Splice Plate Instruction Sheet](#)

Specifications and datasheets

[Eaton Specification Sheet - B54-120 SS4](#)

System overview

[Dura-Green finish overview](#)

Technical service bulletins

[KwikSplice Cable Tray Canada Stocking List Flyer](#)