



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB2125 BAB2125 BKR A *Eaton Corp*

Catalog Number	BAB2125
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 125 A, Non-Interchangeable Tripping Mechanism, Bolt-On, 120/240 V Ac, 4.8 In Overall Height, 3.8 In Overall Length, 2.1 In Overall Width, 0.75 LB
Weight per unit	0.7500 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

amperage rating	125 A
dimensions	3.8000 IN X 2.3000 IN X 4.8000 IN
media	Yes
Poles	2
Trip Type	Non-Interchangeable

Descriptions

Description	BAB2125 BKR A
extra long description	ETN BAB2125 BAB BREAKER 2P 125A MAX
Special Features	Bolt-on mounting

Manufacturer Information

GTIN	00786679303054
UPC	786679303054

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.75

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Conventional Energy - Conventional EnergyResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	CSA Certified,UL Listed