



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



BAB3040H BAB3040H BRKR A

Eaton Corp

Catalog Number	BAB3040H
Manufacturer	Eaton Corp
Description	Thermal Magnetic Circuit Breaker, 40 A, Non-Interchangeable Tripping Mechanism, Bolt-On, 240 V Ac, 4.9 In Overall Height, 3.8 In Overall Length
Weight per unit	1.0 (lbs/each)
Product Category	3 Pole Standard Trip Bolt-On

Features

amperage rating	40 A
dimensions	3.8000 IN X 2.2000 IN X 4.7000 IN
media	Yes
Poles	3
Trip Type	Non-Interchangeable

Descriptions

Description	BAB3040H BRKR A
extra long description	ETN BAB3040H 40A, 3 pole circuit br
Special Features	Bolt-on mounting

Manufacturer Information

GTIN	00786679303405
UPC	786679303405

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	8
Weight Per each	1

Uses, Certifications, and Standards

Application	OtherDatacenters - IT Space: CI and Hyper ConvergedGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyMarine Vessels and Equipment - Marine Vessels and Equipment - OtherResidential Bldgs & Facilities - Residential Bldgs & Facilities - Other
standard	UL Listed,CSA Certified