

# Eaton BR115

Catalog Number: BR115

Eaton BR Thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 15 A, 10 kAIC, Single-pole, 120/240V, BR, #14-4 AWG Cu/Al, BR, Type BR Loadcenters



## General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BR115
	UPC
	786676362054
Product Length/Depth	Product Height
3 in	3 in
Product Width	Product Weight
1 in	0.3 lb
Compliances	Certifications
Federal Specifications Classification W-C375	UL 489

## Type

Type BR 1-Inch plug-on circuit breaker

## Amperage Rating

15 A

## Voltage rating

120/240 V

## Circuit breaker type

BR

## Used with

Type BR Loadcenters

## Mounting Method

Plug-on

## Interrupt rating

10 kAIC

## Main circuit breaker

BR

## Wire size

#14-4 AWG Cu/Al

## Number of poles

Single-pole

## Brochures

[Loadcenters and Circuit Breakers](#)

## Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

## Specifications and datasheets

[Eaton Specification Sheet - BR115](#)