

Eaton BR240

Catalog Number: BR240

Eaton BR Thermal magnetic circuit breaker, Type BR 1-Inch plug-on circuit breaker, 40 A, 10 kAIC, Two-pole, 120/240V, BR, Common breaker trip, #14-4 AWG Cu/Al, Q28, BR, Type BR Loadcenters

General specifications



| | |
|--|-----------------------|
| Product Name | Catalog Number |
| Eaton BR thermal magnetic circuit breaker | BR240 |
| | UPC |
| | 786676363006 |
| Product Length/Depth | Product Height |
| 1.9 in | 2.5 in |
| Product Width | Product Weight |
| 2.9 in | 0.55 lb |
| Compliances | Certifications |
| Federal Specifications Classification W-C375 | UL 489 |

defaultTaxonomyAttributeLabel

Type

Type BR 1-Inch plug-on circuit breaker

Amperage Rating

40 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

BR

Used with

Type BR Loadcenters

Mounting Method

Plug-on

Interrupt rating

10 kAIC

Main circuit breaker

BR

Wire size

#14-4 AWG Cu/Al

Number of poles

Two-pole

Quantity

28

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - BR240](#)