

# Eaton BR3060NQN200

Catalog Number: BR3060NQN200

BR style 1-inch loadcenter, convertible main, ground bar, 200A, single-phase, 40-pole, 40 circuits, 40 spaces, 120/240V, depends upon main breaker kit or main lug kit chosen., NEMA 1 enclosure, I1 box size

## General specifications



Product Name	Eaton BR convertible loadcenter	Catalog Number	BR3060NQN200
UPC	786676026369	Product Length/Depth	3.88 in
Product Height	34.13 in	Product Width	14.31 in
Product Weight	34 lb	Warranty	10 year

## Catalog Notes

The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

## defaultTaxonomyAttributeLabel

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Mounting

Combination

### Number of circuits

60

### Number of spaces

30

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Wire size

Determined by circuit breaker installed

### Box size

G1

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BR3060NQN200](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)