

# Eaton BRP08E200RF

Catalog Number: BRP08E200RF

Eaton BR convertible loadcenter, Feed-through lug, Convertible main, 200 A, X2, Aluminum, Cover included, NEMA 3R, Metallic, 25 kAIC, 16 Circuits, 8 Spaces, Three-wire, Single-phase, 120/240 V

## General specifications



Photo is representative

Product Name

Eaton BR convertible loadcenter

UPC

786689059804

Product Height

5.7 in

Product Weight

18 lb

Certifications

UL 67

UL 50

Catalog Number

BRP08E200RF

Product Length/Depth

5.19 in

Product Width

14.31 in

Warranty

10 year

Catalog Notes

The maximum rating of the panel is the main breaker rating when used as service entrance equipment.

## defaultTaxonomyAttributeLabel

### Special features

Feed-through lug

### Type

Convertible main

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Number of circuits

16

### Number of spaces

8

### Phase

Single-phase

### Voltage rating

120/240 V

### Wire size

#1 AWG-300 kcmil

### Box size

X2

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP08E200RF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)