

# Eaton BRP20N200RG

Catalog Number: BRP20N200RG

Eaton BR convertible loadcenter,Ground bar,Converible,200 A,X5,Aluminum,Cover included,NEMA 3R,Metallic,10 kAIC,BR,Combination,40 Circuits,Single-pole,20 Spaces,Three-wire,Single-phase,Type BR 1-inch breakers,120/240 V



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP20N200RG
UPC	Product Length/Depth
786689059309	3.88 in
Product Height	Product Width
29.13 in	14.31 in
Product Weight	Warranty
19 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

Ground bar

### Type

Converible

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Combination

### Number of circuits

40

### Number Of Poles

Single-pole

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP20N200RG](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)