

# Eaton BRP40B200R

Catalog Number: BRP40B200R

Plug-on neutral main circuit breaker  
loadcenter,200A,X8,Aluminum,Cover included,NEMA  
3R,Metallic,10 kAIC,BR,80 circuits,Single pole,40 spaces,Three-  
wire,Single-phase,Combination,NEMA 3R,Type BR 1-inch  
breakers,120/240V



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP40B200R
UPC	Product Length/Depth
786689059408	39 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

80

### Number Of Poles

Single-pole

### Number of spaces

40

### Phase

Single-phase

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X8

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Drawings

[BR 1 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH M](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP40B200R](#)

NEMA rating  
NEMA 3R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton BRP40B200R

Catalog Number: BRP40B200R

Plug-on neutral main circuit breaker  
loadcenter,200A,X8,Aluminum,Cover included,NEMA  
3R,Metallic,10 kAIC,BR,80 circuits,Single pole,40 spaces,Three-  
wire,Single-phase,Combination,NEMA 3R,Type BR 1-inch  
breakers,120/240V



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP40B200R
UPC	Product Length/Depth
786689059408	39 in
Product Height	Product Width
5.5 in	14.31 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 67	
UL 50	

## defaultTaxonomyAttributeLabel

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Number of circuits

80

### Number Of Poles

Single-pole

### Number of spaces

40

### Phase

Single-phase

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X8

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Drawings

[BR 1 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH M](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP40B200R](#)

NEMA rating  
NEMA 3R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)