

Specifications

Photo is representative

Eaton C25DNF330T

Eaton definite purpose contactor, Mounting plate, Quick, Quick connect (side-by-side), 12 Vac, 50/60 Hz, 15-50A, two- and three-pole, Contactor, Three-pole, Global listed, D1, Box lugs (posidrive setscrew), Non-reversing

General specifications

PRODUCT NAME	Eaton definite purpose contactor
CATALOG NUMBER	C25DNF330T
UPC	782116311422
PRODUCT LENGTH/DEPTH	3.35 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	2.4 in
PRODUCT WEIGHT	1.19 lb
WARRANTY	1 year
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	CSA Certified UL Recognized UL Listed

Product specifications

AMPERAGE RATING	30A
NUMBER OF POLES	Three-pole
TYPE	Non-reversing
AUXILIARY CONTACTS	Pressure plate and quick connect
COIL	24 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
ENCLOSURE	Open with metal mounting plate
FRAME SIZE	15-50 A, two-pole and three-pole
INDUCTIVE FULL LOAD	30 A
MODEL	Contactor
RESISTIVE LOAD	40 A
TERMINALS	Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)
CONNECTION	Quick

Resources

CATALOGS	Motor Control and Protection, Definite Purpose Contactors and Starters, Volume 5, Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - C25DNF330T

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

