

# Eaton C25DNF340H

Catalog Number: C25DNF340H

Eaton definite purpose contactor, Quick, 40A, 12 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 40A, Contactor, Three-pole, 50A, Box lugs (posidrive setscrew) and quick connect terminals , Non-reversing



## General specifications

Product Name	Catalog Number
Eaton definite purpose contactor	C25DNF340H
UPC	Product Length/Depth
782116311682	3.35 in
Product Height	Product Width
3.75 in	2.4 in
Product Weight	Warranty
1.19 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified UL Recognized

## defaultTaxonomyAttributeLabel

### Amperage Rating

40A

### Number Of Poles

Three-pole

### Type

Non-reversing

### Coil

277 Vac, 60 Hz

### Enclosure

Open with metal mounting plate

### Frame size

15-50 A, two-pole and three-pole

### Inductive full load

40 A

### Model

Contactor

### Resistive load

50 A

### Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

### Connection

Quick

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[C25DNF3 3D Model Xchange](#)

[C25DNF3 2D PDF](#)

[C25DNF3 3D Inventor](#)

[C25DNF3 AutoCAD 2D Footprint](#)

[C25DNF3 2D Drawing Xchange](#)

[C25DNF3 AutoCAD 2D Footprint \(mm\)](#)

### Specifications and datasheets

[Eaton Specification Sheet - C25DNF340H](#)