

Eaton C25END430H

Catalog Number: C25END430H

Eaton definite purpose contactor, Quick, 30A, 277 Vac, 60 Hz, Open with metal mounting plate, 15-50A, two- and three-pole, 30A, Contactor, Four-pole, 30A, Screw/pressure plate and quick connect terminals (side-by-side), Non-reversing

General specifications



Product Name	Catalog Number
Eaton definite purpose contactor	C25END430H
UPC	Product Length/Depth
782113578149	3.38 in
Product Height	Product Width
3.75 in	2.68 in
Product Weight	Warranty
2.03 lb	1 year
Compliances	Certifications
RoHS Compliant	CSA Certified UL Recognized
Catalog Notes	
Resistive Load rating per pole	

defaultTaxonomyAttributeLabel

Amperage Rating

30A

Number Of Poles

Four-pole

Type

Non-reversing

Coil

277 Vac, 60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

30 A

Model

Contactors

Resistive load

40 A

Terminals

Screw/pressure plate and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[C25END4 2D Drawing Xchange](#)

[C25END4 AutoCAD 2D Footprint](#)

[C25END4 AutoCAD 2D Footprint \(mm\)](#)

[C25END4 2D PDF](#)

[C25END4 3D Inventor](#)

[C25END4 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - C25END430H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)