

Eaton C25FNF350C

Catalog Number: C25FNF350C

Eaton definite purpose contactor, 60–75A, two- and three-pole ,Open with metal mounting plate ,Box lugs (posidrive setscrew) and quick connect terminals (side-by-side) ,440–480 Vac, 50/60 Hz

General specifications



Product Name

Eaton definite purpose contactor

Catalog Number

C25FNF350C

UPC

782113499666

Product Length/Depth

3.97 in

Product Height

3.75 in

Product Width

2.63 in

Product Weight

1 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

UL Recognized

CSA Certified

Catalog Notes

Resistive Load rating per pole

defaultTaxonomyAttributeLabel

Amperage Rating

60A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

440-480 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

50 A

Model

Contactor

Resistive load

75 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Specifications and datasheets

[Eaton Specification Sheet - C25FNF350C](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)