



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C512HH C Ser 12HR W/Hold Timer *Nsi Industries*

Catalog Number	C512HH
Manufacturer	Nsi Industries
Description	The Tork C512HH 12-Hour Spring-Wound In-Wall Twist Timer With A Commercial-Style Metal Faceplate Is Designed to Control A Variety Of Indoor Appliances, Motors and Lights. Automate Factories, Offices or Other Buildings to Save Energy and Money Using The Simple Twist Knob and Reliable Mechanical Timekeeping. Features A Hold Setting to Keep Power On and Fits Into A Standard Electrical Box For In-Wall Mounting. Designed For SPDT Switch Type On Indoor Loads Such As Ventilation Fans, Lighting, Hvac Systems, Moto
Weight per unit	0.4000 (lbs/each)
Product Category	Electronic Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	12 Hour

Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	C SER 12HR W/HOLD TIMER
extra long description	TORK C512HH Interval Timer 60 Min h
Features	The TORK C412HH spring-wound in-wall twist timer carries our legacy of innovation and quality with reliable timekeeping and consistent performance. Use twist timers to set a countdown for automatically shutting off appliances or lighting, saving you energy and trouble. No more forgetting to turn off a garage light or attic fan: with a twist timer, simply wind the knob to the correct duration and automate the process. TORK twist timers are at home in residential environments or a range of commercial applica
Long Description	The TORK C512HH 12-Hour Spring-Wound In-Wall Twist Timer with a commercial-style metal faceplate is designed to control a variety of indoor appliances, motors and lights. Automate factories, offices or other buildings to save energy and money using the simple twist knob and reliable mechanical timekeeping. Features a HOLD setting to keep power on and fits into a standard electrical box for in-wall mounting. Designed for SPDT switch type on indoor loads such as ventilation fans, lighting, HVAC systems, moto
Product Type	Interval Timer 60 Min Hold Metal
Special Features	With Hold 12 Hour Commercial Grade In Wall Time Switch

Manufacturer Information

Brand	NSi
GTIN	00786261155146
Manufacturers Part Number	C512HH
UPC	786261155146

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Spring Wound In Wall Time Switch-Commercial Grade

Packaging

Carton	1
Weight Per each	0.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	NSI
Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus