

# Eaton CH8B150RF

Catalog Number: CH8B150RF

Eaton CH main breaker loadcenters, Main breaker, 150 A, E, Copper, Not included, NEMA 3R, Metallic, 35 kAIC, CSR, 8, Eight-pole, 8, Three-wire, Single-phase, #2 AWG-300 kcmil, Top/bottom, Flush, 120/240 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CH8B150RF
<b>UPC</b>	<b>Product Length/Depth</b>
782113098425	29.13 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
16 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	Furnished with hub closure plates. Panel includes #4-300 kcmil feed-through lugs. Loadcenter contains single insulated/bondable neutral.

## defaultTaxonomyAttributeLabel

### Type

Main breaker

### Amperage Rating

150 A

### Bus material

Copper

### Cover

Not included

### Main circuit breaker

CSR

### Number of circuits

8

### Number Of Poles

Eight-pole

### Number of spaces

8

### Phase

Single-phase

### Wire size

#2 AWG-300 kcmil

### Feed type

Top/bottom

### Mounting

Flush

### Voltage rating

120/240 V

### Box size

E

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

35 kAIC

## Resources

### Brochures

[Type CH Circuit Breakers and Loadcenters](#)

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CH8B150RF](#)

Number of wires

3



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)