

Eaton CHP22B125X2

Catalog Number: CHP22B125X2

Eaton CH main breaker loadcenters, Main breaker, 125 A, X2, Copper, X2, NEMA 1, Metallic, 10 kAIC, CH, 44, Single-pole, 22, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG, 120/240 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP22B125X2
UPC	Product Length/Depth
786689055158	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
12.3 lb	Limited lifetime
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

Main breaker

Amperage Rating

125 A

Bus material

Copper

Cover

X2

Main circuit breaker

CH

Number of circuits

44

Number Of Poles

Single-pole

Number of spaces

22

Phase

Single-phase

Wire size

#6-1/0 AWG

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP22B125X2](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)