

Eaton CHP42B200R

Catalog Number: CHP42B200R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 200 A, X7, Copper, NEMA 3R, Metallic, CSR, 84, 42, Three-wire, Single-phase, Overhead, 120/240 V



Photo is representative

General specifications

Product Name

Eaton CH main breaker loadcenter

Catalog Number

CHP42B200R

UPC

786689058715

Product Length/Depth

37 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

32 lb

Warranty

Limited lifetime

Certifications

UL 67

UL 50

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

84

Number of spaces

42

Phase

Single-phase

Feed type

Overhead

Voltage rating

120/240 V

Box size

X7

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP42B200R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)