

Eaton CHP42E225X7

Catalog Number: CHP42E225X7

Eaton CH PON 3/4-in Eaton CH loadcenter, 225A, convertible, lugs inst, 42 spaces, NEMA 1, Copper bus, Top/bottom feed, X7, Single phase, three wire



General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP42E225X7
UPC	Product Length/Depth
786679189740	37 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
20.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Purchase Size X7 Cover Separately

defaultTaxonomyAttributeLabel

Type

Convertible, Main Lugs Installed

Amperage Rating

225 A

Bus material

Copper

Cover

X7

Feed type

Top/bottom

Number of circuits

42

Number of spaces

42

Phase

Single-phase

Voltage rating

120/240 V

Box size

X7

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP42E225X7](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)