

Eaton CHP60E225X9

Catalog Number: CHP60E225X9

Eaton CH PON 3/4-inEaton CH loadcenter, 225A, convertible, lugs inst, 60 spaces



General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP60E225X9
UPC	Product Length/Depth
786679189696	45 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
25.35 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Purchase Size X9 Cover Separately
UL 50	

defaultTaxonomyAttributeLabel

Type

Convertible, Main Lugs Installed

Amperage Rating

225 A

Bus material

Copper

Cover

X9

Feed type

Top/bottom

Number of circuits

60

Number of spaces

60

Phase

Single-phase

Voltage rating

120/240 V

Box size

X9

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP60E225X9](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)