



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHU4N7NS Unmetered Surf Pop (1) TT-30R (1) 5-20r2gfi

Eaton Corp

Catalog Number	CHU4N7NS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Unmetered, Unmetered, 30A, 20A, None, Non-Ground Fault, Non-Ground Fault, None, Top, Surface, Circuits: 4, Nema TT-30R, Nema 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None
Weight per unit	16.0 (lbs/each)
Product Category	Unmetered Power Outlet Panels

Features

dimensions	13.6000 IN X 9.5000 IN X 39.9000 IN
------------	-------------------------------------

Dimensions and Weight

Depth	13.6000
Height	39.9000
Width	9.5000

Descriptions

Description	UNMETERED SURF POP (1) TT-30R (1) 5-20R2GFI
extra long description	ETN CHU4N7NS UM SURF POP (1) TT-30R
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount unmetered, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None
Product Type	Um Surf Pop (1) TT-30R (1) 5-20r2gfi

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114203743
Manufacturers Part Number	CHU4N7NS
UPC	782114203743

Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount unmetered

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	16

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588