

Eaton CHU9N9NS

Catalog Number: CHU9N9NS

Eaton pedestal mount unmetered, Water and tamper resistant left/center receptacle, Unmetered, 20A, 20A, None, Non-GF, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA 5-20R2GFI(3), NEMA 5-20R2GFI(3), None, 3, 3, 0, 125V, 125V, None



General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU9N9NS
UPC	Product Length/Depth
786685404233	4.3 in
Product Height	Product Width
17.1 in	9.5 in
Product Weight	Warranty
15 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231
UL Listed file E163588

defaultTaxonomyAttributeLabel

Special features

Water and tamper resistant left/center receptacle

Type

Unmetered

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

None

Receptacle center

NEMA 5-20R2GF

Receptacle left

NEMA 5-20R2GFI

Receptacle right

None

Feed type

Top

Mounting

Surface

Number of circuits

4

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHU9N9NS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)