

Eaton CMB88B200BTS

Catalog Number: CMB88B200BTS

Eaton Cutler Hammer Series , CMB, Residential Meter Breaker, Type CH Non-EUSERC, 200 A, 120/240V, Ring, 8 spaces, 8 circuits, 22 kAIC, Surface mounting, Box size A, Aluminum bus, Overhead/underground feed, Four-jaws, 1 socket

General specifications

Product Name	Catalog Number
Eaton residential meter breaker	CMB88B200BTS
UPC	Product Length/Depth
782114872475	5.38 in
Product Height	Product Width
7 in	14.44 in
Product Weight	Warranty
35.6 lb	Limited lifetime
Certifications	
UL Listed	



Product specifications

Interrupt rating

10 kAIC

Type

All-in-ones

Feed type

Overhead

Utility approvals

NC : Dominion

VA : Dominion

Phase

Single-phase

Number of jaws

Four-jaw

Voltage rating

120/240 V

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Drawings

[Dimensional Drawing - METER BREAKER WEST COAST STYLE](#)

[Dimensional drawing](#)

Specifications and datasheets

[Eaton Specification Sheet - CMB88B200BTS](#)

[Technical Data Residential Meter Breakers: Type CH and BR Residential](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)