

Eaton DG325FGK

Catalog Number: DG325FGK

Eaton General duty cartridge fuse safety switch, 400 A, NEMA 1, Painted steel, Class H fuses, Fusible without neutral, Three-pole, Three-wire, Category: general duty safety switch, 240 V



General specifications

Product Name

Eaton general duty cartridge fuse safety switch

Catalog Number

DG325FGK

UPC

782113589510

Product Length/Depth

7.27 in

Product Height

44.74 in

Product Width

23.08 in

Product Weight

120 lb

Warranty

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

Certifications

UL Listed

Catalog Notes

Maximum hp ratings apply only when dual element fuses are used. Solid neutral bars are not included. Must be ordered separately. Warning! Switch is not approved for service entrance unless a neutral kit is installed.

Physical Attributes

Enclosure

NEMA 1

Enclosure material

Painted steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

General duty, cartridge fused

Performance Ratings

Amperage Rating

400A

Fuse class provision

Class H fuses

Voltage rating

240V

Miscellaneous

Product Category

General duty safety switch

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - DG325FGK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)