

Eaton DG325NRK

Catalog Number: DG325NRK

Eaton General duty cartridge fuse safety switch, 400 A, NEMA 3R, Painted galvanized steel, Class H fuses, Fusible with neutral, Three-pole, Four-wire, Category: general duty safety switch, 240 V



General specifications

Product Name	Catalog Number
Eaton general duty cartridge fuse safety switch	DG325NRK
	UPC
	782113639215

Product Length/Depth	Product Height
7.27 in	44.74 in

Product Width	Product Weight
23.08 in	120 lb

Warranty	Compliances
-----------------	--------------------

Eaton Selling Policy 25-000, one (1) year NEC 230.62 (C) Compliant Barrier from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications
UL Listed

Catalog Notes

Maximum hp ratings apply only when dual element fuses are used

Physical Attributes

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Fusible with neutral

Number Of Poles

Three-pole

Number of wires

4

Type

General duty, cartridge fused

Performance Ratings

Amperage Rating

400A

Fuse class provision

Class H fuses

Voltage rating

240V

Miscellaneous

Product Category

General duty safety switch

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - DG325NRK](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)