# Eaton DH363FRK

# Catalog Number: DH363FRK

Eaton Enhanced visible blade single-throw safety switch, 100 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 30, 40/ 60, 75 hp (1/3PH @480, 600 V), #14-#1/0 Cu/Al

## General specifications



Eaton heavy duty fusible safety switch

e salety switch

UPC

782113206424

**Product Height** 

9 in

**Product Weight** 

21 lb

Catalog Number

DH363FRK

Product Length/Depth

22.5 in

Product Width

12.75 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications Catalog Notes

UL Listed Suitable for service entrance use with a

Neutral Kit installed





### **Physical Attributes**

Enclosure

NEMA 3R

**Enclosure material** 

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

**Number Of Poles** 

Three-pole

Number of wires

3

Type

Heavy duty fusible safety switch

#### Performance Ratings

Amperage Rating

100A

HP rating - max

30, 40/60, 75 hp (1/3PH @480, 600 V)

**NEMA** rating

NEMA 3R

Voltage rating

600 V

#### Miscellaneous

#### **Product Category**

Heavy Duty, Fusible without neutral

#### Resources

#### **Brochures**

Heavy-Duty Safety Switch with Bussmann CUBEFuse Fuse Clips

#### Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH363FRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia