Eaton DH364FRK

Catalog Number: DH364FRK

Eaton Enhanced visible blade single-throw safety switch, 200 A, NEMA 3R, Painted galvanized steel, Class H, Fusible without neutral, Three-pole, Three-wire, 600 V, Max Hp: 50, 50/ 125, 150 hp (1/3PH @480, 600 V), #6-250 kcmil Cu/Al



General specifications

UPC

9.5 in

40 lb

Product Name Catalog Number DH364FRK Eaton heavy duty fusible safety switch Product Length/Depth 782113206790 30 in Product Width **Product Height** 18 in **Product Weight** Warranty Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. Certifications **Catalog Notes** UL Listed Suitable for service entrance use with a

Neutral Kit installed



Physical Attributes

Enclosure

NEMA 3R

Enclosure material Painted galvanized steel

Fuse class provision

Class H

Fuse configuration Fusible without neutral

Number Of Poles Three-pole

Number of wires

3

Туре

Heavy duty fusible safety switch

Performance Ratings

Amperage Rating

200A

HP rating - max 50, 50/ 125, 150 hp (1/3PH @480, 600 V)

NEMA rating NEMA 3R

Voltage rating

600 V

Miscellaneous

Product Category Heavy Duty, Fusible without neutral

Resources

Catalogs Eaton's Volume 2—Commercial Distribution

Specifications and datasheets Eaton Specification Sheet - DH364FRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Right Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia