# Eaton DH365FRK

# Catalog Number: DH365FRK

Eaton Enhanced visible blade single-throw safety switch, 400 A, NEMA 3R, Painted galvanized steel, Class H, Three-pole, Three-wire, 600 V, Max Hp: 250, 350 hp (3PH @480/600 V), (2)#1/0-(2)300 kcmil; or (1)#1/0-(1)750 kcmil Al

## General specifications



Eaton heavy duty fusible safety switch

UPC

782113207216

Product Height

10.25 in

**Product Weight** 

105.8 lb

Catalog Number

DH365FRK

Product Length/Depth

45.5 in

Product Width

24.38 in

Warranty

Eaton Selling Policy 25-000, one (1) year

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

Certifications Catalog Notes

UL Listed Suitable for service entrance use with a

Neutral Kit installed





### **Physical Attributes**

Enclosure

NEMA 3R

**Enclosure material** 

Painted galvanized steel

Fuse class provision

Class H

Fuse configuration

Fusible without neutral

**Number Of Poles** 

Three-pole

Number of wires

3

Type

Heavy duty fusible safety switch

#### Performance Ratings

**Amperage Rating** 

400A

HP rating - max

250, 350 hp (3PH @480/600 V)

**NEMA** rating

NEMA 3R

Voltage rating

600 V

### Miscellaneous

#### **Product Category**

Heavy Duty, Fusible without neutral

#### Resources

#### Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - DH365FRK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia