



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DMW232MV0LTGEB10 Wet Location Fluorescent 2LMP 32W

*Lithonia Lighting*

Catalog Number	DMW232MV0LTGEB10
Manufacturer	Lithonia Lighting
Description	The Lithonia Lighting® 4-Foot, 2-Light White T8 Fluorescent Enclosed and Gasketed Strip Light By Lithonia Lighting Is Ideal Where Dirt, Dust, Humidity and Moisture Are Present
Weight per unit	12.1 (lbs/each)
Product Category	Fluorescent Wet Location Light

### Features

average life	40,000
Ballast Type	Electronic Ballast
Fixture Type	Linear
fixture wattage	64 W
Hardware	Yes
Housing Finish	Gloss
Lamp Type	Fluorescent
Lamp Wattage	32
Material	Fiberglass
Number of Lamps	2
pallet quantity	41
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	1
Wattage	64.0000000000000000

### Material, Color, and Finish

Color	Beige
housing color	Beige
Housing Material	Fiberglass
Lens Color	WHITE
Lens Material	Acrylic

### Dimensions and Weight

Height	5.5
Length	50
Width	9.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	WET LOCATION FLOURESCENT 2LMP 32W
extra long description	LITH DMW 2 32 MVOLT GEB10IS Enclose
Long Description	The Lithonia Lighting® 4-foot, 2-light white T8 fluorescent enclosed and gasketed strip light by Lithonia Lighting is ideal where dirt, dust, humidity and moisture are present
Product Type	Linear

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00784231151099
Manufacturers Part Number	DMW 2 32 MVOLT GEB10IS
UPC	784231151099

## Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	LINEAR

## Trade Size

aperture size	4FT
---------------	-----

## Packaging

Carton	1
Weight	12
Weight Per each	12.1

## Uses, Certifications, and Standards

Application	Automotive & Parking,Education,Enclosed & Gasketed,Government,Healthcare,Hospitality,House of Worship,Manufacturing,Offices & Banks,Power & Gas,Retail,Special Applications,Sports and Recreation,Transportation,Warehouses
environmental conditions	Demanding,Indoor
Mounting	Surface,Suspended
standard	CSA,UL