

Eaton DPU222RGF20WRTR

Catalog Number: DPU222RGF20WRTR

Air Conditioning Disconnect, Non-fused pullout, 20A weather/tamper-resistant ground fault receptacle, 60A, 120/240V, 10 kAIC, #14-3 Cu/Al 60°C or 75°C, NEMA 3R Galvanized Steel enclosure, 10 hp at 240V, ANSI 61 gray

General specifications



Product Name

Eaton air conditioning disconnect

Catalog Number

DPU222RGF20WRTR

UPC

786685375274

Product Length/Depth

7.5 in

Product Height

13 in

Product Width

4.75 in

Product Weight

8 lb

Certifications

CSA Certified
UL Listed

defaultTaxonomyAttributeLabel

Type

Non-fused pullout

Amperage Rating

60A

Horsepower

10 hp at 240 V

Voltage rating

120/240 V

Wire size

#14-3 AWG Cu/Al

Color

ANSI 61 gray

Enclosure

NEMA 3R

Enclosure material

Galvanized steel

Interrupt rating

10 kAIC

Receptacle

20 A weather/tamper-resistant ground fault receptacle

Resources

Brochures

[Air Conditioning Disconnects](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - DPU222RGF20WRTR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)