Eaton DT224URK

Catalog Number: DT224URK

Eaton Heavy duty double-throw non-fused safety switch, 200 A, NEMA 3R, Painted galvanized steel, Non-fusible, Two-pole, Twowire, 240 Vac, 250 Vdc

General specifications



Catalog Number

Eaton heavy duty double-throw non-

DT224URK

fused safety switch

UPC

782113713380

Product Length/Depth

Product Height

11.26 in

37.69 in

Product Width

Product Weight

19.15 in

80 lb

Warranty

Certifications

Eaton Selling Policy 25-000, one (1) year UL Listed

from the date of installation of the


Catalog Notes

Product or eighteen (18) months from the

Suitable for service entrance use with a

date of shipment of the Product,

neutral or ground lug kit installed







default Taxonomy Attribute Label

Type

Heavy Duty, Double-Throw

Amperage Rating

200A

Number Of Poles

Two-pole

Voltage rating

240 Vac, 250 Vdc

Enclosure

NEMA 3R

Enclosure material

Painted galvanized steel

Fuse configuration

Non-fusible

Number of wires

2

Resources

Brochures

Double-throw safety switch

Expanded double-throw safety switch line

Catalogs

Eaton's Volume 2—Commercial Distribution

Switching devices catalog

Multimedia

Switching Devices Flex Center

ARMS Enclosed Circuit Breaker

Double Up on Safety

Specifications and datasheets

Eaton Specification Sheet - DT224URK



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.







Eaton.com/socialmedia